

## With Folding Handle Open Design




Please complete item number:

**L** Base of drawer with center opening.  
Facilitates removal and insertion.

**V** Base of drawer closed.



## With Folding Handle Closed Design



Please complete item number:

**L** Base of drawer with center opening.  
Facilitates removal and insertion.

**V** Base of drawer closed.



## EPPI® 45 + 50 Drawer Racks • with Folding Handle

Useful for EPPI® 45 + 50 and all boxes up to external dimensions 133x133x53 mm (WxDxH). Front closed.

With Safety Stop				
Cat. No.	L	Number	DxH	
	V			
		Depth	Height	(mm)
SE50-22NAM	■	2	2	301 x 123
SE50-23NAM	■	2	3	301 x 184
SE50-24NAM	■	2	4	301 x 245
SE50-25NAM	■	2	5	301 x 306
SE50-26NAM	■	2	6	301 x 367
SE50-27NAM	■	2	7	301 x 428
SE50-32NAM	■	3	2	434 x 123
SE50-33NAM	■	3	3	434 x 184
SE50-34NAM	■	3	4	434 x 245
SE50-35NAM	■	3	5	434 x 306
SE50-36NAM	■	3	6	434 x 367
SE50-37NAM	■	3	7	434 x 428
SE50-42NAM	■	4	2	567 x 123
SE50-43NAM	■	4	3	567 x 184
SE50-44NAM	■	4	4	567 x 245
SE50-45NAM	■	4	5	567 x 306
SE50-46NAM	■	4	6	567 x 367
SE50-47NAM	■	4	7	567 x 428
SE50-52NAM	■	5	2	700 x 123
SE50-53NAM	■	5	3	700 x 184
SE50-54NAM	■	5	4	700 x 245
SE50-55NAM	■	5	5	700 x 306
SE50-56NAM	■	5	6	700 x 367
SE50-57NAM	■	5	7	700 x 428

Without Safety Stop				
Cat. No.	L	Number	DxH	
	V			
		Depth	Height	(mm)
SE50-22NAO	■	2	2	283 x 116
SE50-23NAO	■	2	3	283 x 173
SE50-24NAO	■	2	4	283 x 231
SE50-25NAO	■	2	5	283 x 288
SE50-26NAO	■	2	6	283 x 346
SE50-27NAO	■	2	7	283 x 403
SE50-32NAO	■	3	2	416 x 116
SE50-33NAO	■	3	3	416 x 173
SE50-34NAO	■	3	4	416 x 231
SE50-35NAO	■	3	5	416 x 288
SE50-36NAO	■	3	6	416 x 346
SE50-37NAO	■	3	7	416 x 403
SE50-42NAO	■	4	2	549 x 116
SE50-43NAO	■	4	3	549 x 173
SE50-44NAO	■	4	4	549 x 231
SE50-45NAO	■	4	5	549 x 288
SE50-46NAO	■	4	6	549 x 346
SE50-47NAO	■	4	7	549 x 403
SE50-52NAO	■	5	2	682 x 116
SE50-53NAO	■	5	3	682 x 173
SE50-54NAO	■	5	4	682 x 231
SE50-55NAO	■	5	5	682 x 288
SE50-56NAO	■	5	6	682 x 346
SE50-57NAO	■	5	7	682 x 403

## EPPI® 45 + 50 Drawer Racks • with Folding Handle

Useful for EPPI® 45 + 50 and all boxes up to external dimensions 133x133x53 mm (WxDxH). Front closed.

With Safety Stop				
Cat. No.	L	Number	DxH	
	V			
		Depth	Height	(mm)
SE50-22GAM	■	2	2	311 x 123
SE50-23GAM	■	2	3	311 x 184
SE50-24GAM	■	2	4	311 x 245
SE50-25GAM	■	2	5	311 x 306
SE50-26GAM	■	2	6	311 x 367
SE50-27GAM	■	2	7	311 x 428
SE50-32GAM	■	3	2	444 x 123
SE50-33GAM	■	3	3	444 x 184
SE50-34GAM	■	3	4	444 x 245
SE50-35GAM	■	3	5	444 x 306
SE50-36GAM	■	3	6	444 x 367
SE50-37GAM	■	3	7	444 x 428
SE50-42GAM	■	4	2	577 x 123
SE50-43GAM	■	4	3	577 x 184
SE50-44GAM	■	4	4	577 x 245
SE50-45GAM	■	4	5	577 x 306
SE50-46GAM	■	4	6	577 x 367
SE50-47GAM	■	4	7	577 x 428
SE50-52GAM	■	5	2	710 x 123
SE50-53GAM	■	5	3	710 x 184
SE50-54GAM	■	5	4	710 x 245
SE50-55GAM	■	5	5	710 x 306
SE50-56GAM	■	5	6	710 x 367
SE50-57GAM	■	5	7	710 x 428

Without Safety Stop				
Cat. No.	L	Number	DxH	
	V			
		Depth	Height	(mm)
SE50-22GAO	■	2	2	293 x 116
SE50-23GAO	■	2	3	293 x 173
SE50-24GAO	■	2	4	293 x 231
SE50-25GAO	■	2	5	293 x 288
SE50-26GAO	■	2	6	293 x 346
SE50-27GAO	■	2	7	293 x 403
SE50-32GAO	■	3	2	426 x 116
SE50-33GAO	■	3	3	426 x 173
SE50-34GAO	■	3	4	426 x 231
SE50-35GAO	■	3	5	426 x 288
SE50-36GAO	■	3	6	426 x 346
SE50-37GAO	■	3	7	426 x 403
SE50-42GAO	■	4	2	559 x 116
SE50-43GAO	■	4	3	559 x 173
SE50-44GAO	■	4	4	559 x 231
SE50-45GAO	■	4	5	559 x 288
SE50-46GAO	■	4	6	559 x 346
SE50-47GAO	■	4	7	559 x 403
SE50-52GAO	■	5	2	692 x 116
SE50-53GAO	■	5	3	692 x 173
SE50-54GAO	■	5	4	692 x 231
SE50-55GAO	■	5	5	692 x 288
SE50-56GAO	■	5	6	692 x 346
SE50-57GAO	■	5	7	692 x 403

## With Hand Grip Open Design




Please complete item number:

- B** Sides of the drawers approx. 10 mm high. Front with hand grip approx. 40 mm high. Examination of contents possible.
- F** Sides of the drawers approx. 20 mm high. Front with hand grip to max. height, closed. No examination of contents possible.




## With Hand Grip Closed Design



















































Please complete item number:

- B** Sides of the drawers approx. 10 mm high. Front with hand grip approx. 40 mm high. Examination of contents possible.
- F** Sides of the drawers approx. 20 mm high. Front with hand grip to max. height, closed. No examination of contents possible.



















































## EPPI® 45 + 50 Drawer Racks • with Hand Grip

Useful for EPPI® 45 + 50 and all boxes up to external dimensions 133x133x53 mm (WxDxH). Base of drawers closed.

With Safety Stop						Without Safety Stop					
Cat. No.	B	Number		DxH		Cat. No.	B	Number		DxH	
	F	Depth	Height	(mm)			F	Depth	Height	(mm)	
SE50-22N	 MV	2	2	301 x 123		SE50-22N	 OV	2	2	301 x 116	
SE50-23N	 MV	2	3	301 x 184		SE50-23N	 OV	2	3	301 x 173	
SE50-24N	 MV	2	4	301 x 245		SE50-24N	 OV	2	4	301 x 231	
SE50-25N	 MV	2	5	301 x 306		SE50-25N	 OV	2	5	301 x 288	
SE50-26N	 MV	2	6	301 x 367		SE50-26N	 OV	2	6	301 x 346	
SE50-27N	 MV	2	7	301 x 428		SE50-27N	 OV	2	7	301 x 403	
SE50-32N	 MV	3	2	434 x 123		SE50-32N	 OV	3	2	434 x 116	
SE50-33N	 MV	3	3	434 x 184		SE50-33N	 OV	3	3	434 x 173	
SE50-34N	 MV	3	4	434 x 245		SE50-34N	 OV	3	4	434 x 231	
SE50-35N	 MV	3	5	434 x 306		SE50-35N	 OV	3	5	434 x 288	
SE50-36N	 MV	3	6	434 x 367		SE50-36N	 OV	3	6	434 x 346	
SE50-37N	 MV	3	7	434 x 428		SE50-37N	 OV	3	7	434 x 403	
SE50-42N	 MV	4	2	567 x 123		SE50-42N	 OV	4	2	567 x 116	
SE50-43N	 MV	4	3	567 x 184		SE50-43N	 OV	4	3	567 x 173	
SE50-44N	 MV	4	4	567 x 245		SE50-44N	 OV	4	4	567 x 231	
SE50-45N	 MV	4	5	567 x 306		SE50-45N	 OV	4	5	567 x 288	
SE50-46N	 MV	4	6	567 x 367		SE50-46N	 OV	4	6	567 x 346	
SE50-47N	 MV	4	7	567 x 428		SE50-47N	 OV	4	7	567 x 403	
SE50-52N	 MV	5	2	700 x 123		SE50-52N	 OV	5	2	700 x 116	
SE50-53N	 MV	5	3	700 x 184		SE50-53N	 OV	5	3	700 x 173	
SE50-54N	 MV	5	4	700 x 245		SE50-54N	 OV	5	4	700 x 231	
SE50-55N	 MV	5	5	700 x 306		SE50-55N	 OV	5	5	700 x 288	
SE50-56N	 MV	5	6	700 x 367		SE50-56N	 OV	5	6	700 x 346	
SE50-57N	 MV	5	7	700 x 428		SE50-57N	 OV	5	7	700 x 403	

## EPPI® 45 + 50 Drawer Racks • with Hand Grip


Useful for EPPI® 45 + 50 and all boxes up to external dimensions 133x133x53 mm (WxDxH). Base of drawers closed.

With Safety Stop						Without Safety Stop					
Cat. No.	B	Number		DxH		Cat. No.	B	Number		DxH	
	F	Depth	Height	(mm)			F	Depth	Height	(mm)	
SE50-22G	 MV	2	2	311 x 123		SE50-22G	 OV	2	2	311 x 116	
SE50-23G	 MV	2	3	311 x 184		SE50-23G	 OV	2	3	311 x 173	
SE50-24G	 MV	2	4	311 x 245		SE50-24G	 OV	2	4	311 x 231	
SE50-25G	 MV	2	5	311 x 306		SE50-25G	 OV	2	5	311 x 288	
SE50-26G	 MV	2	6	311 x 367		SE50-26G	 OV	2	6	311 x 346	
SE50-27G	 MV	2	7	311 x 428		SE50-27G	 OV	2	7	311 x 403	
SE50-32G	 MV	3	2	444 x 123		SE50-32G	 OV	3	2	444 x 116	
SE50-33G	 MV	3	3	444 x 184		SE50-33G	 OV	3	3	444 x 173	
SE50-34G	 MV	3	4	444 x 245		SE50-34G	 OV	3	4	444 x 231	
SE50-35G	 MV	3	5	444 x 306		SE50-35G	 OV	3	5	444 x 288	
SE50-36G	 MV	3	6	444 x 367		SE50-36G	 OV	3	6	444 x 346	
SE50-37G	 MV	3	7	444 x 428		SE50-37G	 OV	3	7	444 x 403	
SE50-42G	 MV	4	2	577 x 123		SE50-42G	 OV	4	2	577 x 116	
SE50-43G	 MV	4	3	577 x 184		SE50-43G	 OV	4	3	577 x 173	
SE50-44G	 MV	4	4	577 x 245		SE50-44G	 OV	4	4	577 x 231	
SE50-45G	 MV	4	5	577 x 306		SE50-45G	 OV	4	5	577 x 288	
SE50-46G	 MV	4	6	577 x 367		SE50-46G	 OV	4	6	577 x 346	
SE50-47G	 MV	4	7	577 x 428		SE50-47G	 OV	4	7	577 x 403	
SE50-52G	 MV	5	2	710 x 123		SE50-52G	 OV	5	2	710 x 116	
SE50-53G	 MV	5	3	710 x 184		SE50-53G	 OV	5	3	710 x 173	
SE50-54G	 MV	5	4	710 x 245		SE50-54G	 OV	5	4	710 x 231	
SE50-55G	 MV	5	5	710 x 306		SE50-55G	 OV	5	5	710 x 288	
SE50-56G	 MV	5	6	710 x 367		SE50-56G	 OV	5	6	710 x 346	
SE50-57G	 MV	5	7	710 x 428		SE50-57G	 OV	5	7	710 x 403	



## EPPI® 32 Drawer Racks


### With Hand Grip Open Design <sup>1)</sup>



**Example:** Cat. No. SE32-38NBMV  
For 24 x EPPI® 32 Boxes.  
**With** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x434x325 mm

## EPPI® 37 Drawer Racks


### With Hand Grip Open Design <sup>1)</sup>



**Example:** Cat. No. SE37-46NBMV  
For 24 x EPPI® 37 Boxes.  
**With** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x567x274 mm

## EPPI® 70 + 75 Drawer Racks

### With Folding Handle Open Design <sup>1)</sup>




**Example:** Cat. No. SE75-33NAML  
For 9 x EPPI® 75 Boxes.  
**With** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x434x254 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.


**V** Base of drawer closed. See illustrations on page 38

## EPPI® 70 + 75 Drawer Racks

### With Hand Grip Version B <sup>3)</sup> Open Design <sup>1)</sup>




**Example:** Cat. No. SE75-22NBVOV  
For 4 x EPPI® 75 Boxes.  
**Without** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x301x163 mm



- <sup>1)</sup> All drawer racks can also be supplied with a closed design (See illustrations on page 38 +39). Please enquire if needed.
- <sup>2)</sup> All drawer racks can be produced as a combo drawer rack for shallower boxes (e.g. EPPI® 50) to exploit the interior space of uprights to the maximum.
- <sup>3)</sup> The drawer inserts can also be supplied in a modified design »F«. See page 39 for an explanation of the differences.

## EPPi® 80 Drawer Racks

**With Folding Handle**  
**Open Design <sup>1)</sup>**



**Example:** Cat. No. **SE80-42NAOL**  
For 8 x FPPI® 80 Boxes.


**Without** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x549x170 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.

**V** Base of drawer closed.  
See *illustrations on page 38*

## EPPi® 80 Drawer Racks

**With Hand Grip**  
**Version B** <sup>3)</sup>  
**Open Design** <sup>1)</sup>




**Example:** Cat. No. **SE80-53N****B**MV  
For 15 x FPPI® 80 Boxes

**With** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x700x265 mm

## EPPi® 95 + 96 Drawer Racks

## With Folding Handle Open Design <sup>1)</sup>



**Example:** Cat. No. **SE96-43NAOL**  
For 12 x EPPI® 96 Boxes.


**Without** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x549x305 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.

**V** Base of drawer closed.  
See *illustrations on page 38*

## EPPi® 95 + 96 Drawer Racks

**With Hand Grip**  
**Version B** <sup>3)</sup>  
**Open Design** <sup>1)</sup>




**Example:** Cat. No. **SE96-33N****B**MV  
For 9 x EPPi® 96 Boxes.

**With** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x434x316 mm

## EPPi® 102 Drawer Racks

**With Folding Handle  
Open Design <sup>1)</sup>**



**Example:** Cat. No. **SE102-32NAML**  
For 6 x EPPI® 102 Boxes.


**With** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x434x223 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.

**V** Base of drawer closed.  
See illustrations on page 38

## EPPi® 102 Drawer Racks

**With Hand Grip**  
**Version B** <sup>3)</sup>  
**Open Design** <sup>1)</sup>




**Example:** Cat. No. **SE102-52N****B**OV  
For 10 x EPPI® 102 Boxes.

**Without** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x700x216 mm

Footnotes <sup>1)</sup> and <sup>2)</sup> and <sup>3)</sup> see page 40.

## EPPI® 105 Drawer Racks

### With Folding Handle Open Design <sup>1)</sup>




**Example:** Cat. No. SE105-43NAML  
For 12 Boxes up to a height of 105 mm  
(e.g. EPPI® 105).  
**With** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x567x340 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.  
**V** Base of drawer closed. See illustrations on page 38

## EPPI® 105 Drawer Racks


### With Hand Grip Version **B** <sup>3)</sup> Open Design <sup>1)</sup>



**Example:** Cat. No. SE105-32NBMV  
For 6 Boxes up to a height of 105 mm  
(e.g. EPPI® 105).  
**With** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x434x227 mm

## EPPI® 128 Drawer Racks

### With Folding Handle Open Design <sup>1)</sup>




**Example:** Cat. No. SE128-22NAOL  
For 4 Boxes up to a height of 128 mm  
(e.g. EPPI® 128).  
**Without** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x283x267 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.  
**V** Base of drawer closed. See illustrations on page 38

## EPPI® 128 Drawer Racks


### With Hand Grip Version **B** <sup>3)</sup> Open Design <sup>1)</sup>



**Example:** Cat. No. SE128-33NBV  
For 9 Boxes up to a height of 128 mm  
(e.g. EPPI® 128).  
**Without** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x434x400 mm

## EPPI® 133 Drawer Racks

### With Folding Handle Open Design <sup>1)</sup>




**Example:** Cat. No. SE133-22NAML  
For 4 Boxes up to a height of 133 mm  
(e.g. BRAVO 130).  
**With** safety stop. Base of drawers open.  
Dimensions: WxDxH = 140x301x283 mm

**L** Base of drawer with center opening. Facilitates removal and insertion.  
**V** Base of drawer closed. See illustrations on page 38

## EPPI® 133 Drawer Racks

### With Hand Grip Version **B** <sup>3)</sup> Open Design <sup>1)</sup>



**Example:** Cat. No. SE133-53NBV  
For 15 Boxes up to a height of 133 mm  
(e.g. BRAVO 130).  
**Without** safety stop. Base of drawers closed.  
Dimensions: WxDxH = 140x700x413 mm

Footnotes <sup>1)</sup> and <sup>2)</sup> and <sup>3)</sup> see page 40.